

theBoom[®] Quiet

Whisper and be heard



Owner's Manual



www.theBoom.com

Thank you for being a customer of theBoom Quiet.

theBoom Quiet is a high-end audio headset for the discriminating buyer. It affords you a level of freedom and privacy not possible with other products. You can speak softly into theBoom Quiet, comfortable in the knowledge that you will be heard clearly.

Use theBoom Quiet to enjoy high quality audio entertainment or to communicate effectively, even in noisy environments. The Boom Quiet has many additional features to provide you the best in comfort and convenience.

We hope this manual serves to help you get the most out of your new product.

What's in the box




- 1 Works with most cell phones. A different connector is provided if required, based on your cell phone make and model. A PC connector is available, sold separately.
- 2 Volume control adjusts hearing volume. If it is turned down all the way, make sure to turn it up to get good hearing volume.
- 3 The mute button mutes the microphone when pressed down and held in that position. When released, it unmutes the microphone.




PC connector
(sold separately)

theBoom Quiet Quick Start Guide

How to use theBoom Quiet as a headset for your cell phone or PC




Insert Boom microphone into "mic" jack




Insert universal adapter into "audio in" jack

For use with cell phone



Connect universal adapter to cell phone adapter

For use with PC




Plug into PC sound card's audio out jack

Plug into PC sound card's mic jack


Connect universal adapter to PC adapter

theBoom Quiet features theBoom noise cancelling technology in the microphone that allows you to communicate clearly even in very noisy environments.

How to use theBoom Quiet as stereo headphones



Remove Boom microphone




portable music player

cd player

airplane audio plug

Plug this end into audio out jack



Insert stereo headphones adapter into "audio in" jack

Using the Active Noise Reduction (ANR)

The Boom Quiet is equipped with state-of-the-art ANR technology that is designed to target and cancel out background noise while providing exceptional acoustic playback performance. Turning the ANR on creates a quiet listening environment inside the ear cups, allowing for a rich sound experience. To activate the ANR, locate the power switch on the left ear cup, just above the volume control knob, and push it to the ON position. Even while not listening to music or other audio, you can use the ANR feature to get some quiet restful sleep on an airplane.

Using the ANR function



Flip switch to "ON" position to activate ANR;
Green indicator light comes on

Using the volume control



Volume control adjusts your hearing volume

The hearing volume control knob is located on the left ear cup.

Please note that the volume setting has no effect on noise reduction.

theBoom Quiet Care Instructions


Folding your headset for carrying




Hold headset as shown with the "notch" facing away from you



Bend outwards at the top hinge



Fold out all the way until the two halves are touching



Fold the ear cups inwards and press band and cups together with fingers and thumbs

When folded in this fashion, theBoom Quiet is most compact, and can be carried in the provided soft leather pouch. In this configuration, it can conveniently be carried inside small hand bags or briefcases. In order to carry it within the storage case that it came in, you will need to unfold it and fold it "flat", as you found it when you first opened the case. For maximum protection, carry the headset within its storage case.

Installing the batteries for ANR



Hold the left earcup (the one with "open" marked on it)



Push down with thumb and slide downwards towards the arrow



Flip open lid to reveal battery compartment, and install batteries.

2 AAA batteries are required (included) to power the ANR (Active Noise Reduction) function in the headphones.

theBoom Technology

Whisper and be heard™

On Wall Street ...

theBoom Quiet is a product of UmeVoice, Inc., the makers of [theBoom](#) award-winning headset for mobile professionals. The noise-cancelling technology was created to enable reliable speech recognition as well as clear communications on the noisy floors of Wall Street.



In the Military ...

Enabling the clearest communication for the military, used in the C130 airplane fleet and other air, sea and land applications.

Listen to theBoom in Blackhawk helicopter noise at www.theboom.com

In Racing ...

We outfitted a Ferrari with theBoom technology; the engine could not be heard by the pit crew communicating with the driver even when the car was driven at 200 mph!





You can just "whisper and be heard"
and not disturb your neighbor.



Even from a noisy cafe, the
person you are calling will
think you are in a quiet office.



Even road noise is eliminated.



Plug into your PC or laptop for the
clearest VoIP calls you've ever made.

Email: info@theboom.com

UmeVoice, Inc.
20C Pimentel Ct., Suite 1
Novato, CA 94949
Phone: 888.230.3300
Fax: 415.883.1711

www.theBoom.com